


Vertical Rack Bonding Busbar



Vertical Rack Bonding Busbar (RBB) for consolidating equipment bonding connections. Constructed of 5/8" H x 1/4" W (15.9 mm x 6.4 mm) hard-drawn electrolytic tough pitch 110 alloy copper bar with pairs of #1/4-20 tapped mounting holes on 5/8" (15.9 mm) centers. The 36" L (910 mm) bar has one set of #5/16 self-clinching studs on 1" (25.4 mm) centers at one end for attachment of a bonding conductor. The 72" L (1830 mm) bar has two sets of #5/16 self-clinching studs on 1" (25.4 mm) centers at both ends for attachment of a bonding conductor.

- Each package contains one Vertical Rack Bonding Busbar
- Vertical Rack Busbars with insulators and lug kits are also available
- Other configurations are available on request
- UL® Listed, File E236184, Category KDER (US), KDER7 (Canada) - Grounding and Bonding Equipment



ORDERING INFORMATION

Part Number	Description	Number of Lugs	Shipping Weight lb (kg)
40160-036	5/8 x 1/4 x 36 (15.88 x 6.4 x 910)	8	4 (1.8)
40160-072	5/8 x 1/4 x 72 (15.88 x 6.4 x 1830)	13	5 (2.3)

Note: Busbars are 1/4" (6.4 mm) thick.

United States

Agoura Hills, CA
800-834-4969

Canada

Toronto, Ontario, Canada
+905-850-7770

Europe

Buckinghamshire, UK
+441628524834

Middle East & Africa

Dubai, UAE
+971-4-2602125

Doha, Qatar
+974-4-267422

Latin America

+52-55-5203-7525
Toll Free within Mexico
800-201-7592
chatsworth.com.co

Asia Pacific

+86 21 6880-0266
chatsworth.com.cn



CHATSWORTH
PRODUCTS